



Model NO.	DC-084
Schematic	
CIRCUIT DIAGRAM	



Model NO.			
PIN	Ø2.0	Ø2.35	Ø2.5

					TOLERANCE UNLESS SPECIFIED					
					UP TO 5mm: ±0.1	ANGULAR	1			
					ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS	BY APPD
6					TITLE: DC JACK		UNIT : MM	ROHS	DWN	
5					MODEL: DC-084 Ø 2.0		SCALE: 1:1	COMPLIANT	CHK'D	
4	SPRING	STEEL	1	SN-PLATED	东莞市六钧电子五金有限公司				APPD	
3	CENTER PIN	BRASS	1	SN-PLATED						
2	BUSHING	BRASS	1	Ni-PLATED						
1	HOUSING	PA66	1							
NO.	PART NAME	MATERIAL	QTY	FINISHING					PRO.AGL: 	REV :A0