



REV.	DESCRIPTION	ECN NO.	NAME	DATE

技术要求Specification:

1. 材质Material: PA66 UL94V-0;
2. 额定电流 Current rating:3.0A AC,DC
3. 额定电压 Voltage rating:250V AC,DC
4. 温度范围 Temperature range:-25℃to+85℃
5. 接触电阻 Contact resistance:<20mΩ
6. 绝缘电阻Insulation resistance:>1000MΩ
7. 耐压Withstand voltage:1000V AC/minute
8. 塑件表面平整光洁,无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。
Plastic surface smooth and clean, no obvious burrs,bubbles, distortion, gate strain, lack of material and otherundesirable phenomena.

Part No	Pin	A	B	C	D
WF-1D254A2P	2	2.50	5.70	3.70	3.70
WF-1D254A3P	3	5.00	8.20	6.20	6.20
WF-1D254A4P	4	7.50	10.70	8.70	8.70
WF-1D254A5P	5	10.00	13.20	11.20	11.20
WF-1D254A6P	6	12.50	15.70	13.70	13.70
WF-1D254A7P	7	15.00	18.20	16.20	16.20
WF-1D254A8P	8	17.50	20.70	18.70	18.70
WF-1D254A9P	9	20.00	23.20	21.20	21.20
WF-1D254A10P	10	22.50	25.70	23.70	23.70
WF-1D254A11P	11	25.50	28.20	26.20	26.20
WF-1D254A12P	12	27.50	30.70	28.70	28.70
WF-1D254A13P	13	30.00	33.20	31.20	31.20
WF-1D254A14P	14	32.50	35.70	33.70	33.70
WF-1D254A15P	15	35.50	28.20	36.20	36.20
WF-1D254A16P	16	37.50	40.70	38.70	38.70

GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				
DIM. TOL.	TITLE: XH2.5MM HOUSING				
X	±0.30				DWG. NO.: WF-1D254ANP
X.X	±0.25				DRAWN: MAX
X.XX	±0.15				CHECKED: ELLA
X.XXX	±0.15				PART NO.: WF-1D254ANP
GENERAL ANGLE:	±3°				APPROVED: WILL
UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	

BXCONN[®]

