



A		B		C		D		E	
REV.	DESCRIPTION				ECN NO.	NAME	DATE		

1





技术要求Specification:

1. 材质Material: PA66 UL94V-0;
2. 额定电流 Current rating:2.0A AC,DC
3. 额定电压 Voltage rating:100V AC,DC
4. 温度范围 Temperature range:-25℃to+85℃
5. 接触电阻 Contact resistance:$\leq 20m\Omega$
6. 绝缘电阻Insulation resistance:$\geq 1000M\Omega$
7. 耐压Withstand voltage:800V AC/minute
8. 塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs, bubbles.distortion, gate strain, lack of material and other undesirable phenomena.


2



Part No	Pin	A	B	C
WF-1D200A2P	2	2.00	5.70	4.50
WF-1D200A3P	3	4.00	7.70	6.50
WF-1D200A4P	4	6.00	9.70	8.50
WF-1D200A5P	5	8.00	11.70	10.50
WF-1D200A6P	6	10.00	13.70	12.50
WF-1D200A7P	7	12.00	15.70	14.50
WF-1D200A8P	8	14.00	17.70	16.50
WF-1D200A9P	9	16.00	19.70	18.50
WF-1D200A10P	10	18.00	21.70	20.50
WF-1D200A11P	11	20.00	23.70	22.50
WF-1D200A12P	12	22.00	25.70	24.50
WF-1D200A13P	13	24.00	27.70	26.50
WF-1D200A14P	14	26.00	29.70	28.50
WF-1D200A15P	15	28.00	31.70	30.50
WF-1D200A16P	16	30.00	33.70	32.50

3

4



5

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			
DIM.	TOL.	TITLE: PH2.0MM HOUSING			
X		DWG. NO.: WF-1D200ANP		DRAWN: MAX	
X.X	±0.30	PART NO.: WF-1D200ANP		CHECKED: ELLA	
X.XX	±0.25	UNIT: mm		SCALE: none	APPROVED: WILL
X.XXX	±0.15	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	
GENERAL ANGLE: ±3°					

