



REV.	DESCRIPTION	ECN NO.	NAME	DATE

Part No	Pin	A	B
WF-1B254B2P-R	2	2.50	7.50
WF-1B254B3P-R	3	5.00	10.00
WF-1B254B4P-R	4	7.50	12.50
WF-1B254B5P-R	5	10.00	15.00
WF-1B254B6P-R	6	12.50	17.50
WF-1B254B7P-R	7	15.00	20.00
WF-1B254B8P-R	8	17.50	22.50
WF-1B254B9P-R	9	20.00	25.00
WF-1B254B10P-R	10	22.50	27.50
WF-1B254B11P-R	11	25.00	30.00
WF-1B254B12P-R	12	27.50	32.50
WF-1B254B13P-R	13	30.00	35.00
WF-1B254B14P-R	14	32.50	37.50
WF-1B254B15P-R	15	35.00	40.00
WF-1B254B16P-R	16	37.50	42.50
WF-1B254B17P-R	17	40.00	45.00
WF-1B254B18P-R	18	42.50	47.50
WF-1B254B19P-R	19	45.00	50.00
WF-1B254B20P-R	20	47.50	52.50

技术要求:

1. 塑件材料: PA66(UL-94V-0)
2. 接触件: 黄铜镀锡
3. 接触电阻: $\leq 10m\Omega$
4. 绝缘电阻: $\geq 100M\Omega$
5. 额定电压: 250V AC DC
6. 额定电流: 2.0A AC DC
7. 耐压: 能承受 1000V AC/Minute
8. 工作温度: $-25^{\circ} \sim +85^{\circ}$
9. 可焊性试验: 浸锡面积 $\geq 95\%$ 温度 235 , 时间 2.5 ± 0.5 秒
10. 铅和镉等六大有害物质含量要符合环保要求.

2	Contact	Brass	n*1	电镀(锡): 整个表面镀层30u"MIN, 再镀80u"MIN.
1	Wafer	PA66(UL94V-0)	1	红色
序号	名称	材料	数量	备注
GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD		
DIM. TOL.		TITLE: WAFER XHB2.54MM 带扣 弯针 红色		
X		DWG. NO.: WF-1B254BNP-R		
X.X		DRAWN: MAX		
X.XX		CHECKED: ELLA		
X.XXX		PART NO.: WF-1B254BNP-R		
GENERAL ANGLE: $\pm 3^{\circ}$		APPROVED: WILL		
UNIT: mm		SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4
		LAYER: bxconn		

BXCONN[®]

