




P. C. B LAYOUT  
BOTTOM VIEW

SPECIFICATION

- 1、Electrical rating : DC 15V 5A
- 2、Contact resistance : <math>< 20m\Omega</math>(initial)
- 3、Insulation resistance : >1000M $\Omega$   
(500VDC between open contacts)
- 4、Dielectric strength : >1500V 1 minute
- 5、Electrical life : 6000 cycles
- 6、Temperature rise at the terminal : Max.30 $^{\circ}$ C
- 7、Solder ability of terminal : Max350 $^{\circ}$ C,3S(no pressure may be placed in the terminals when soldering by hand)
- 8、Any Cd Pb Hg etc and it's compounds is not include in this product

PIN	$\phi 2.0$	$\phi 2.5$
APPD		

					TOLERANCE UNLESS SPECIFIED						
					UP TO 5mm: $\pm 0.1$	ANGULAR					
					ABOVE 5mm: $\pm 0.2$	$\pm 1^{\circ}$	NO	DATE	REVISIONS	BY	APPD
5	PIN	BRASS	1	Ni-PLATED							
4	TERMINAL	COPPER ALLOY	3	Ag/Sn-PLATED							
3	CONTACT	COPPER ALLOY	1	Ag-PLATED							
2	ACTUATOR	PA66	1	BLACK							
1	HOUSING	PA66	1	BLACK							
					TITLE: DC JACK			UNIT : MM	ROHS	DWN	
					MODEL: SS01-BBI-1+DC-005-1-01			SCALE: 1:1	COMPLIANT	CHK'D	
					 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 HOOYA 东莞市弘皓电子有限公司					APPD	
NO.	PART	NAME	MATERIAL	QTY	FINISHING				PRO.AGL:	 	REV :A0