


P.C.B LAYOUT



SPECIFICATION

1. Rating : DC 12V 2A.
2. Contact resistance: ≤50mΩ.
3. Insulation resistance: ≥100MΩ (DC250V).
4. Withstanding voltage: 250VAC .
5. Insertion and extraction force: 5-35N
5. life test: 5000 cycles.
6. Operation temperature range: -25℃~85℃.
7. Sign "*" is importance dimension.

10	铜后盖	BRASS	1	Sn-PLATED
9	铜前盖	BRASS	1	Sn-PLATED
8	右中针	BRASS	1	Sn-PLATED
7	左中针	BRASS	1	Sn-PLATED
6	右长针	BRASS	1	Sn-PLATED
5	左长针	BRASS	1	Sn-PLATED
4	右短针	BRASS	1	Sn-PLATED
3	左短针	BRASS	1	Sn-PLATED
2	盖子	PBT	1	
1	底座	PBT	1	
NO.	PART NAME	MATERIAL	QTY	FINISHING

TOLERANCE UNLESS SPECIFIED									
		<1.5: ±0.1mm	ANGULAR	A1	2018.3.29	更新图面			
>1.5~5.0: ±0.25mm	±1°	NO	DATE	REVISIONS			BY	APPD	
>5.0: ±0.3mm		TITLE: DIN JACK		UNIT : MM	ROHS COMPLIANT	DWN			
		MODEL: DIN-603		SCALE: 1:1		CHK'D			
东莞市六钧电子五金有限公司						APPD			
						PRO.AGL:	⊕	REV :A1	