



主要技术特性要求:

1.使用温度范围:

环境温度:  $-25 \sim +70^{\circ}\text{C}$

相对湿度: 95%( $40^{\circ}\text{C}$ )

2.额定负荷: 2A 100V AC

3.接触电阻:  $\leq 30\text{n}\Omega$

4.绝缘电阻:  $\geq 100\text{M}\Omega$

5.耐压: 500V AC (50Hz) 1min

6.插拔力: 10~50N

7.寿命:  $\geq 5000$ 次

NO.	PART NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED		A1	2021.11.26	更新绝缘盖材质PCB为PBT	WM	BY	APPD
					UP TO 5mm: $\pm 0.1$	ANGULAR $\pm 1^{\circ}$						
8	绝缘盖	PBT	1									
7	右长针	BRASS	1	Sn-PLATED								
6	左长针	BRASS	1	Sn-PLATED								
5	左短针	BRASS	1	Sn-PLATED								
4	直针	BRASS	1	Sn-PLATED								
3	右短针	BRASS	1	Sn-PLATED								
2	接地针	PBS	1	Sn-PLATED								
1	底座	PBT	1	BLACK								
					TITLE: DIN JACK			UNIT : MM	ROHS COMPLIANT	DWN		
					MODEL: DIN-504B-M10			SCALE: 1:1		CHK'D		
					东莞市六钧电子五金有限公司					APPD		
										PRO.AGL:		REV :A1