

RoHS

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance:20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40°C to +105°C

Contact Material:Brass





Contact Plating:Au Or Tin Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

P	3	D	2	24	1	5	00	4
产品类型 P=排针	间距 3=2.54	塑胶高度 D=2.5	排数 2=双排	单排PIN数 1~40P	产品形态 1=DIP	塑胶材料 1=PBT 2=LCP 5=PA6T	电镀厚度 00=常规 01=1u" 02=2u" 03=3u"	包装方式 1=管装 2=卷装 3=盘装 4=袋装 5=盒装

0051
序列号

2.54±0.1

0.64 SQ

OPERATION

DRAW

X.X

±0.30

X.XX

±0.20

X.XXX

±0.10

Angle

±3°

DIM

TOL

APPROVE

SCALE

FIT

UNIT

mm

SIZE

A4

SHEET

1/1

PROJ.

◆

深圳市连盛精密连接器有限公司

PART NO.

1010301172

TITLE:

2.54PH H=2.5 2*24P DIP PA6.0
PC3.0 L=11.5 AU0.6U PA6T

1

2

3

4

5

6

7

8

9