


PANEL CUTOUT DETAIL



P.C.B LAYOUT

					TOLERANCE UNLESS SPECIFIED								
					UP TO 5mm: ±0.1	ANGULAR	A0	2019.11.12	初版		GYW		
					ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD	
5	DIN323C-5#SPRING	SUS	1	Ni PLATED	东莞市六钧电子五金有限公司			UNIT : MM	ROHS	DWN			
4	DIN323H-3# CONTACT PIECES	BRASS	1	Au PLATED				SCALE: 2:1	COMPLIANT	CHK'D			
3	DIN323H-2# CONTACT PIECES	BRASS	1	Au PLATED						APPD			
2	DIN323H-1# CONTACT PIECES	BRASS	1	Au PLATED									
1	DIN323C CASE	PA66	1	BLACK									
NO.	PART NAME	MATERIAL	QTY	FINISHING				PRO.AGL:		REV :A0			