


主要技术特性要求:

1. 使用温度范围:
环境温度: $-25 \sim +70^{\circ}\text{C}$
相对湿度: 95%(40 $^{\circ}\text{C}$)
2. 额定负荷: 2A 100V AC
3. 接触电阻: $\leq 30\text{m}\Omega$
4. 绝缘电阻: $\geq 100\text{M}\Omega$
5. 耐压: 500V AC (50Hz) 1min
6. 插拔力: 10~50N
7. 寿命: ≥ 5000 次



				TOLERANCE UNLESS SPECIFIED							
				UP TO 5mm: ± 0.1	ANGULAR	1					
				ABOVE 5mm: ± 0.2	$\pm 1^{\circ}$	NO	DATE	REVISIONS		BY	APPD
4	CONTACT FOOT	BRASS	2	Ag-Plated	TITLE: DIN SOCKET			UNIT : MM	ROHS COMPLIANT	DWN	
3	CONTACT FOOT	BRASS	4	Ag-Plated	MODEL: DIN-449			SCALE: 1:1		CHK'D	
2	COVER	PBT	1	BLACK	东莞市六钧电子五金有限公司					APPD	
1	HOUSING	PBT	1	BLACK						PRO.AGL:	
NO.	PART NAME	MATERIAL	QTY	FINISHING							