

1、基本資料 / Basic Information

主要材质信息 / Materials:

触刀 / Contacts: 镀锡紫铜 / Tin plated copper


端帽 / Terminals: 镀锡黄铜 / Tin plated brass

管体 / Body: 陶瓷管 / Ceramic

熔体 / Fuse element: 纯银 / Pure silver

填料 / Filler: 高纯度石英砂 / Pure silicon sand

2 、外形及安装尺寸/Shapes and DimenSions



Unit: mm

型号 / Part no.	A	B	C	D	E	F	G	H	I
HDRFB26	78	57	30	20	23	26	14	9	3

3、基本参数 / Basic Parameters

管号 Body size	额定电流 Rated current (A)	I ² t (A ² s)		功率损耗 Power loss (W)	分断能力 Breaking Capability
		弧前 I ² t Pre-arcing	熔断 I ² t I ² t		
HDRFB26	10	6	68	1.8	100KA(250Vac) 20KA(150Vdc)
	16	20	210	2.5	
	20	25	260	4	
	25	5.6	40	4	
	32	7	67	5	
	40	8	100	6	
	50	10.5	160	7	
	63	11.8	290	9	
	80	19	390	10	
	100	22.5	680	10	
	125	27.5	1350	16	
	160	35.5	2200	20	
	200	40	3400	28	

4、时间电流特性/Time-current characteristics

