





SCHEMATIC



P.C.B LAYOUT
TOP VIEW



H=XXmm

					TOLERANCE UNLESS SPECIFIED		NO	DATE	REVISIONS		BY	APPD
					<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°			TITLE: TACT SWITCH		UNIT : MM	ROHS COMPLIANT
6	STEM	BRASS		1				A1	2024.4.9	△ 按实物增加材质PI膜/盖子无电镀	MLQ	
5	COVER	SUS		1	△							
4	TAPE	PI △		1	YELLOW							
3	CONTACT	SUS		1	Ag-Plated							
2	TERMINAL	BRASS		4	Ag-Plated							
1	HOUSING	LCP		1	BLACK							
NO.	PART	NAME	MATERIAL	QTY	FINISHING							

东莞市六钧电子五金有限公司

PRO.AGL: REV :A1

SPECIFICATION

1. Rating : DC12V 50mA.
2. Contact resistance: ≤100mΩ.
3. Insulation resistance: ≥100MΩ (DC100V).
4. Withstanding voltage: 250VAC .
5. Operating Force: /250±80gf
6. Travel:0.15±0.1mm.
7. life test: 10,000 cycles.
8. Operation temperature range:-25℃~85℃.
9. Sign "*" is importance dimension.