





CIRCUIT DIAGRAM



NOTE:
Rating: DC 12V 0.1A
Operating Force: ≤36gf
Lifetime: 50,000 Cycles

⑤	Center Spring	—	1	Phosphor Bronze	Ag Plated	—
④	Base	—	1	PA	Black	—
③	Terminal	—	4	Brass	Ag Plated	—
②	Cover	—	1	SUS	Natural	—
①	Knob	—	1	PA	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE					
DRAWN		LIUCAN	2023.9.12					
CHECKED				TITLE:		DETECTOR SWITCHS		
APPROVALS				PART NO.		K5-1679SA-01		
D.	TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
			10~30	±0.20				
			5~10	±0.15				
			~ 5	±0.10				
		±2°	DRAWING NO.		_____	SHEET 1 OF 1		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
—	A	—	NEW	—	—	—