








SCHEMATIC



PCB LAYOUT



H=2.5/2.7mm

					TOLERANCE UNLESS SPECIFIED						
6	MYLAR	PET	1	YELLOW	UP TO 5mm:±0.1	ANGULAR	A1	2023.5.31	增加H2.7图面△		MLQ
5	SPRING	SUS	2	Ag-Plated	ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS		BY APPD
4	CONTACT FOOT	BRASS	2	Ag-Plated	TITLE: TACT SWITCH			UNIT : MM	ROHS	DWN	
3	COAT	SUS	1	Ni-Plated	MODEL: TS-1107防尘			SCALE: 1:1	COMPLIANT	CHK'D	
2	BUTTON	PA66	1		 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司			APPD			
1	HOUSING	PA6T	1					PRO.AGL: 		REV :A1	
NO.	PART NAME	MATERIAL	QTY	FINISHING							