








1. 电路 CIRCUIT: ON/OFF
2. 额定值 RATING: 10A 125/250VAC(UL;C-UL)
12 (4) A 250V~T85/55 (ENEC17;NEMKO;CQC;KC)
3. 接触电阻 CONTACT RESISTANCE: <50mΩ
4. 绝缘电阻 INSULATION RESISTANCE: >100MΩ (500VDC
BETWEEN OPEN CONTACTS)
5. 耐电压 DIELECTRIC STRENGTH: >1500VAC 0.5mA 1 MINUTE



PANEL CUTOUT DIMENSION TABLE



电话: 0769-82310511-867
邮箱: hooya89@hooya.hk

品 名	规 格
SS21-CWIBF3-L39-R	白盖 白座 绿灯
SS21-CWIBF3-L42-R	白盖 白座 蓝灯

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM			
4	→	9	→	RANGE	TOLERANCE			WFB 2018.05.31	LMC 2019.07.10	SCALE	NO			
3	→	8	→	X	±0.30					MAT'L	***			
2	→	7	→	X.X	±0.20					MATERIAL NO.		DRAWING NO.	REV.	
1	→	6	→	X.XX	±0.10									
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	LEGION ELECTRONIC & HARDWARE CO., LTD.					SS21-CWIBF3-L39-R		*****	A0