







Projection(P)



Short(S)



SECTION A-A



SPECIFICATION

Contact Rating: 25mA,24V DC
Contact Resistance: 50mΩ max
Insulation Resistance: 100mΩ min.500V DC
Dielectric Strength: 500V AC/1minute
Operating Force: 1000gf max
Travel: 2mm
Operating Life: 3000cycles
Operating Temp: -20℃~+70℃
Storage Temp: -40℃~+80℃

PART NO.	N0.OF POS	DIM.A	DIM.B
DS-01	1	4.06	
DS-02	2	6.6	2.54
DS-03	3	9.14	5.08
DS-04	4	11.68	7.62
DS-05	5	14.22	10.16
DS-06	6	16.76	12.7
DS-07	7	19.3	15.24
DS-08	8	21.84	17.78
DS-09	9	24.38	20.32
DS-10	10	26.92	22.86
DS-12	12	32	27.94

4	Terminal		Copper Alloy	T: Tin plated G: Plating Gold≥15MU
3	Base	1	PBT	Black
2	Keystake	1	PBT	white
1	Cover	1	PBT	Black Blue Red
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

DSWB XX LHGET

Packing: T: Tube R: Reel
Finish: E: 1u-3u F: 10u
Finish G: Full Gold S: Contat Gold plated
Terminal S: SMD H: Straight
Actuator T: (Tape sealed) S: (Low profile W/O Tape) L: (Extension)
HP: Half-Pitch IC: IC PV: Piano WB: WB

		new		2015/5/3		A		瀚源			
ECN BO.		DESCRIPTION.		DATE.		REV.					
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER				SCALT: 1/2		SCALE: 3:1		
Mikey	Tom	Jerry	PART NAME	DSWBXXLHGET		UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X. ±0.25			
			MODEL NAME	DSWBXXLHGET				X.x ±0.20			
			3RD ANGLE PROJ	HanElectricity Co.,LTD					X.xx ±0.15		
								ANGULAR ±3°			
								FILE.NO.			