



一. 电气性能:

- 1-1. 额定电流: 3A AC DC.
- 1-2. 绝缘电阻: $\geq 500M\Omega$ Min
- 1-3. 耐 压: 300V AC/Minute

二. 物理特性:

- 2-1. 操作温度: $-40^{\circ}C \sim 105^{\circ}C$

三. 材质:

- 3-1. 塑胶: PBT(Black) UL94V-0
- 3-2. 插针: Brass/Gold plated

$n \geq 2$ 的自然数 单排PIN数

—		new		2015/5/3	A	瀚源
ECN BO.		DESCRIPTION.		DATE.	REV.	
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	2541FV-XXP-B	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X. ±0.25
			MODEL NAME	2541FV-XXP-B		X.x ±0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx ±0.15
					FILE.NO.	±3