



Technical data:

Housing :PBT(UL94V-0).Black

Terminal:S. Q0.64mm Brass,Gold plating

Current Rating :1Amp Max.

Dielectric Withstanding Voltage:

600V AC R.M.S. for one minute.

Insulation Resistance :5000M ohms Min

AT 500V DC

Contact Resistance :30m ohms Max.

Operating Temperature :-55℃ to+105℃

Max Processing Temp :220℃ for 10 seconds.

Dimension

position	A	B	C
06	15.24	13.04	5.08
08	17.78	15.58	7.62
10	20.32	18.12	10.16
12	22.86	20.66	12.70
14	25.40	23.20	15.24
16	27.94	25.74	17.78
18	30.48	28.28	20.32
20	33.02	30.82	22.86
22	35.56	33.36	25.40

position	A	B	C
24	38.10	35.90	27.94
26	40.64	38.44	30.48
30	45.72	43.52	35.56
34	50.80	48.60	40.64
40	58.42	56.22	48.26
50	71.12	68.92	60.96
60	83.82	81.62	73.66
64	88.90	86.70	78.74

_____		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER				SCALT: 1/2	SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	HY2541WV-N-2xXXP	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X.	±0.25	
			MODEL NAME	HY2541WV-N-2xXXP			X.x	±0.20	
							X.xx	±0.15	
			3RD ANGLE PROJ	HanElectricity Co.,LTD				ANGULAIR	±3
								FILE.NO.	