


材质 Material:

绝缘体 Insulator: Glass filled PBT UL94V-0 ,Black

接触件 Contacts: Brass

电镀层 Plating: All Nickel plating

电气性能 Electrical Characteristics:

接触电阻 Contact Resistance: 20mΩmax. at DC 100mA

绝缘电阻 Insulator Resistance: 1000MΩmin. at 500V DC

耐压 Withstanding Voltage: 1000V AC/rms 50Hz For 1 minute

工作电流 Current Rating: 2 AMP

使用温度范围 Operating Temperature: -55℃~+105℃

电缆规格 Cable: 1.27mm (0.050") pitch flat cable

9555W	Nylon UL94V-0	Brass	Tin Plated	9555H-2xXXA
Series No.	Material	Material	Metal plating	Mate with Housing

Dimension			
Positor	A	B	C
2x03	12.22	5.08	6.35
2x04	14.76	7.62	8.89
2x05	17.3	10.16	11.43
2x07	22.38	15.24	16.51
2x08	24.92	17.78	19.05
2x10	30	22.86	24.13
2x12	35.08	27.94	29.21
2x13	37.62	30.48	31.75
2x15	42.7	35.56	36.83
2x17	47.78	40.64	41.91
2x20	55.4	48.26	49.53
2x25	68.1	60.96	62.23
2x30	80.8	73.66	74.93
2x34	85.88	78.74	80.01

_____		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER				SCALT: 1/2	SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	9555H-2xXXA		UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X.	±0.25	
			MODEL NAME	9555H-2xXXA			X.x	±0.20	
							X.xx	±0.15	
			3RD ANGLE PROJ	HanElectricity Co.,LTD				ANGULAIR	±3
								FILE.NO.	