










Specifications:

1.Electrical:

- 1.1 Current Rating:1. 8A/contact terminal
- 1.2 Voltage Rating:30V DC
- 1.3 Contact Resistance:50 milliohms Max
- 1.4 Dielectric Withstanding Voitage:300 V AC AT Sea Levo
- 1.5 Insulation resistance:100MEGA ohms MIN

2.Mechanical:

- 2.1 Cnnector Mate and Unmate ForceMate force:3. 0kgf (Max)Unmate force:0. 7kgf (MIN)
- 2.2 Durability:2000 cycles



3.Material:

- 3.1 Housing:Hing Temperature Tnermaplastics, U1 94V-0 LCP Black
- 3.2 Contact C5191-EH
- 3.3 She11: H65 EHO.3MM

4. PLATING

- 4. 1 Contact: Plated Gold in Mating Area; Tin On Solder Talls
- 4.2 Shell:Nickel 50u"Min Plated.

05XX-4BH23-X
 1:AU 1U"
 6:AU 30U"
 T:TIN
 N:NICKEL
 S:Scrolls F:Flat



S:Scrolls

		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER				SCALT: 1/2	SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	05XX-4BH23-X		UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X. ±0.25	
			MODEL NAME	05XX-4BH23-X				X.x ±0.20	
			3RD ANGLE PROJ	HanElectricity Co.,LTD					X.xx ±0.15
								ANGULAIR ±3	
							FILE.NO.		