



弯针



直针



技术参数

耐电压: 500VAC/60S
接触电阻: $\leq 20\text{m}\Omega$
绝缘电阻: $\geq 1000\text{m}\Omega$
额定电流: 3A
环境温度: $-55^{\circ}\sim 120^{\circ}$
焊接温度时间: $\leq 235^{\circ}$, $\leq 3\text{s}$
保持力: $\geq 1.5\text{kg/芯}$
可焊性: $\geq 95\%$ 面积
塑胶: PBT
触点材质: 黄铜-镀金

9555W	Nylon UL94V-0	Brass	Tin Plated	9555H-2xXXA
Series No.	Material	Material	Metal plating	Mate with Housing

_____		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER				SCALT: 1/2	SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	9555WV-2xXXA		UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X.	±0.25	
			MODEL NAME	9555WV-2xXXA			X.x	±0.20	
					X.xx		±0.15		
			3RD ANGLE PROJ	HanElectricity Co.,LTD				ANGULAIR	±3
								FILE.NO.	