








Electrical Characteristics:  
Current rating:0.4A AC/DC  
Voltage rating:50V AC/DC  
Temperature range: -25℃~+85℃  
Withstand Voltage:200V AC/Minute  
Contact Resistance: ≤20mΩ  
Insulation resistance: ≥500MΩ



SECTION A-A



适用扁平线



适用线路板

| 编号 | 尺寸 (mm) |       |       | 编号 | 尺寸 (mm) |       |       |
|----|---------|-------|-------|----|---------|-------|-------|
|    | A       | B     | C     |    | A       | B     | C     |
| 4  | 1.50    | 2.59  | 6.39  | 35 | 17.03   | 18.12 | 21.92 |
| 5  | 2.00    | 3.09  | 6.89  | 36 | 17.53   | 18.62 | 22.42 |
| 6  | 2.50    | 3.59  | 7.39  | 37 | 18.03   | 19.12 | 22.92 |
| 7  | 3.00    | 4.09  | 7.89  | 38 | 18.53   | 19.62 | 23.42 |
| 8  | 3.50    | 4.59  | 8.39  | 39 | 19.03   | 20.12 | 23.92 |
| 9  | 4.00    | 5.09  | 8.89  | 40 | 19.53   | 20.62 | 24.42 |
| 10 | 4.50    | 5.59  | 9.39  | 41 | 20.04   | 21.12 | 24.92 |
| 11 | 5.01    | 6.09  | 9.89  | 42 | 20.54   | 21.62 | 25.42 |
| 12 | 5.51    | 6.59  | 10.39 | 43 | 21.04   | 22.12 | 25.92 |
| 13 | 6.01    | 7.09  | 10.89 | 44 | 21.54   | 22.63 | 26.43 |
| 14 | 6.51    | 7.60  | 11.40 | 45 | 22.04   | 23.13 | 26.93 |
| 15 | 7.01    | 8.10  | 11.90 | 46 | 22.54   | 23.63 | 27.43 |
| 16 | 7.51    | 8.60  | 12.40 | 47 | 23.04   | 24.13 | 27.93 |
| 17 | 8.01    | 9.10  | 12.90 | 48 | 23.54   | 24.63 | 28.43 |
| 18 | 8.51    | 9.60  | 13.40 | 49 | 24.04   | 25.13 | 28.93 |
| 19 | 9.01    | 10.10 | 13.90 | 50 | 24.54   | 25.63 | 29.43 |
| 20 | 9.51    | 10.60 | 14.40 | 51 | 25.05   | 26.13 | 29.93 |
| 21 | 10.02   | 11.10 | 14.90 | 52 | 25.55   | 26.63 | 30.43 |
| 22 | 10.52   | 11.60 | 15.40 | 53 | 26.05   | 27.13 | 30.93 |
| 23 | 11.02   | 12.10 | 15.90 | 54 | 26.55   | 27.64 | 31.44 |
| 24 | 11.52   | 12.61 | 16.41 | 55 | 27.05   | 28.14 | 31.94 |
| 25 | 12.02   | 13.11 | 17.91 | 56 | 27.55   | 28.64 | 32.44 |
| 26 | 12.52   | 13.61 | 17.41 | 57 | 28.05   | 29.14 | 32.94 |
| 27 | 13.02   | 14.11 | 17.91 | 58 | 28.55   | 29.64 | 33.44 |
| 28 | 13.52   | 14.61 | 18.41 | 59 | 29.05   | 30.14 | 33.94 |
| 29 | 14.02   | 15.11 | 18.91 | 60 | 29.55   | 30.64 | 34.44 |
| 30 | 14.52   | 15.61 | 19.41 |    |         |       |       |
| 31 | 15.03   | 16.11 | 19.91 |    |         |       |       |
| 32 | 15.53   | 16.61 | 20.41 |    |         |       |       |
| 33 | 16.03   | 17.11 | 20.91 |    |         |       |       |
| 34 | 16.53   | 17.62 | 21.42 |    |         |       |       |

| 序号 | 名称 | 数量 | 材料  | 附注      |
|----|----|----|-----|---------|
| 1  | 塑件 | 1  | LCP | 本色      |
| 2  | 锁扣 | 1  | LCP | 黑色      |
| 3  | 插簧 | N  | 磷铜  | 镍底, 高亚锡 |
| 4  | 焊片 | 2  | 磷铜  | 镍底, 高亚锡 |

| _____    |         | new          |                | 2015/5/3   |                        | A           |            | 瀚源         |  |
|----------|---------|--------------|----------------|------------|------------------------|-------------|------------|------------|--|
| ECN BO.  |         | DESCRIPTION. |                | DATE.      |                        | REV.        |            |            |  |
| DESIGNED | CHECKED | APPROVAL     | DRAWING NUMBER |            |                        | SCALT: 1/2  |            | SCALE: 3:1 |  |
| Mikey    | Tom     | Jerry        | PART NAME      | 05A20LXX   | UNLESS OTHERWISE       |             | X. ±0.25   |            |  |
|          |         |              | MODEL NAME     | H-05A20LXX | SPECIFIED,TOLERANCE:   |             | X.x ±0.20  |            |  |
|          |         |              | 3RD ANGLE PROJ |            | HanElectricity Co.,LTD |             | X.xx ±0.15 |            |  |
|          |         |              |                |            |                        | ANGULAR ±3° |            | FILE.NO.   |  |