



Part Number : 1300980236

Series Number : 130098

Product Category : Cable Grips

Product Description : MAX-LOC Strain Relief Cord-Sealing Grip, 3/4" NPT, Straight Male, Cable Diameter 6.35-9.53mm (.250-.375")

Status : Active

Engineering Number : 5622

Documents & Resources

Drawings
Drawing 1300980236_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Cable Grips
Series	130098
Description	MAX-LOC Strain Relief Cord-Sealing Grip, 3/4" NPT, Straight Male, Cable Diameter 6.35-9.53mm (.250-.375")
NEMA Rating	NEMA 3R
Product Family	Strain-Relief Cord Grips
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678872104

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	6.35-9.53mm (.250-.375")
Color - Grommet	Gray
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Net Weight	450.000/g
Number of Holes	1
O-Ring	No
Thread Size	3/4" NPT

Use with Part(s)

Description	Part Number
-------------	-------------

MAX-LOC Lock Nut 3/4" NPT	/content/molex/molex-dot-com/us/en/products/product-page.html/1300990144.html
MAX-LOC Gasket Sealing Ring, 3/4" NPT, Black	/content/molex/molex-dot-com/us/en/products/product-page.html/1300990150.html
MAX-LOC O-Ring, 3/4" NPT	/content/molex/molex-dot-com/us/en/products/product-page.html/1301800333.html