



Part Number : 1300030048

Series Number : 130003

Product Category : Circular Industrial Connectors

Product Description : Quick-Change Receptacle, 4 Pole, 1/2" - 14 NPT, Male (Straight) to 14 AWG Leads, 0.30m (11.81") Length

Status : Active

Engineering Number : 32632

---

## Documents & Resources


### Drawings

Drawing 1300030048\_sd.pdf

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

## General

Status	Active
Category	Circular Industrial Connectors
Series	130003
Description	Quick-Change Receptacle, 4 Pole, 1/2" - 14 NPT, Male (Straight) to 14 AWG Leads, 0.30m (11.81") Length
IP Rating	IP67
Product Family	Brad Quick-Change Connectors
Product Name	Quick-Change
Type	Single Ended (pigtail)
UPC	78678832632

## Agency

CSA	LR6837
UL	E46237

## Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	600V AC/DC

## Physical

Coupling Type	External Thread
Gender	Male
Keyway	Single
Length	0.305m
Material - Component	Nylon
Mounting Thread Size	1/2" - 14 NPT
Net Weight	199.000/g
Orientation	Straight
Panel Mount	Front
Poles	4
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 1015
Wire Size (AWG)	14

---

---

This document was generated on Apr 12, 2024