

RoHS

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance:20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40°C to +105°C

Contact Material:Brass





Contact Plating:Au Or Tin Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

P	3	D	2	25	1	5	00	X
产品类型 P=排针	间距 3=2.54	塑胶高度 D=2.5	排数 2=双排	单排PIN数 1~40P	产品形态 1=DIP	塑胶材料 1=PBT 2=LCP 5=PA6T	电镀厚度 00=常规 01=1u" 02=2u" 03=3u"	包装方式 1=管装 2=卷装 3=盘装 4=袋装 5=盒装

0051
序列号

				OPERATION		DRAW			SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30					UNIT		
				X.XX	±0.20	CHECK			SIZE	A4	PART NO.	1010300060
A0	2012.03.28	NEW DRAWING		X.XXX	±0.10					SHEET		
				Angle	±3°	APPROVE					TITLE:	2.54PH H=2.5 2x25P DIP PA6.0 PC3.0 L=11.5 AU0.6U PA6T
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL					PROJ.		