





SAMZO REAC/ROHS

REV	ECN NO	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	Replace frame			2013.06.21



P. C. B LAYOUT



- ◆ SPECIFICATIONS
- Current rating: 3A AC, DC
 - Voltage rating: 250V AC, DC
 - Temperature range: -40°C ~ +105°C
 - Insulation resistance: 1000MΩ Min.
 - Withstanding voltage: 1000V AC/ minute.
 - Contact resistance: 20mΩ Max.

A. SERISE: 6T-XHB WITH LOCK
 B. SPACING: L-2.50mm
 C. MOUNTING: D-WT
 D. STANDARD: A-WAFER
 E: PIN: 02-2P (02-16P)
 F: CODE: 0-REGULAR

6T L D A ** 0
 A B C D E F

孔数	型号	尺寸 (mm)		
		A	B	C
2	XHB-2AWT	2.5	7.5	10.0
3	XHB-3AWT	5.0	10.0	12.5
4	XHB-4AWT	7.5	12.5	15.0
5	XHB-5AWT	10.0	15.0	17.5
...
16	XHB-16AWT	37.5	42.5	45.0

ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR					
1	针脚	黄铜	N	镀锡					
2	主体	LCP	1	XXX			GENERAL TOLERANCE		
2	焊片	磷铜	2	镀锡			≥0~2<	±0.15	
					DESIGN	WANGUIFA	2018.06.12	≥2~5<	±0.25
					CHECKED	ZHENGUILAN	2018.06.12	≥0~2<	±0.15
					APPROVED	LILIANJIANG	2018.06.14	≥5	±0.35

FIRST VIEW

SCALE 1:1 UNIT mm

The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts. WWW.KKK-JP.COM

SAMZO COMPONENTS
 Electronic switch and connector manufacturer

TITLE: XHB2.50-WITH LOCK
DWG NO: 6TLD-P2502
PART NO: 6TLD25022
MODEL NO: 6TLDA-**-*
NAME: WAFER CONNECTOR