





PCB LAYOUT

SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 30mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer Nylon66
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
HY-02A	2.00	6.00
HY-03A	4.00	8.00
HY-04A	6.00	10.00
HY-05A	8.00	12.00
HY-06A	10.00	14.00
HY-07A	12.00	16.00
HY-08A	14.00	18.00
HY-09A	16.00	20.00
HY-10A	18.00	22.00
HY-11A	20.00	24.00
HY-12A	22.00	26.00
HY-13A	24.00	28.00
HY-14A	26.00	30.00
HY-15A	28.00	32.00

GENERL TOLERANCE		制 图 (DR.)	林月旺		料 号 PART NO.	HY-NA		版 本 REV.	A			
X.±0.25	X."±2"	审 核 (CHK.)	李攀进		品 名 TITLE	HY直针座		页 次 SHEET	1/1			
.X±0.20	.X"±1"				客户料号 CUTM. NO.							
.XX±0.15	.XX"±0.5"	核 准 (APPD.)	罗观彬									
.XXX±0.10	.XXX"±0.5"	单 位 UNITS	MM	比 例 SCALE	深圳市富港科技有限公司							
				1:1								