

RoHS

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance:20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40℃ to +105℃

Contact Material:Brass





Contact Plating:Au Or Tin Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230℃ for 30-60 seconds
(260℃ for 10 seconds)

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

P 3 D 1 13 1 5 00 4 2193

产品类型
P=排针

间距
3=2.54

塑胶高度
D=2.5

排数
1=单排

单排PIN数
1~40P

产品形态
1=DIP

塑胶材料
5=PA6T

电镀厚度
00=常规

包装方式
1=管装
2=卷装
3=盘装
4=袋装
5=盒装

序列号

OPERATION

DRAW

CHECK

APPROVE

SCALE

FIT

UNIT

mm

SIZE

A4

SHEET

1/1

PROJ.

◆

深圳市连盛精密连接器有限公司

PART NO.

1010301408

TITLE:

2.54PH H=2.5 1*13P DIP PA6.0
PC3.0 L=11.5 AU0.6U PA6T

REV

DATE

MODIFICATION DESCRIPTION

CHANGE

1

2

3

4

5

6

7

8

9