



P	LTR	DESCRIPTION	DATE	DWN	APVD
	2	INFORMATION ADDED TO SHEET 2	01OCT2020	SM	MZ
	3	DRAFTING UPDATE	29OCT2020	SM	MZ
	A	PRODUCT UNDER TESTING	24NOV2020	SM	MZ
	AI	18AWG WIRE SIZE ADDED	27JAN2022	DM	SM

NOTES:

CONTACTS SUPPLIED SEPARATELY ON REELS, MUST PURCHASED ACCORDING TO WIRE SIZES. BELOW ARE THE CONTACT PART NUMBERS:

CONTACT P/N	WIRE SIZE
2359527-1	1.5mm ² TO 2.5mm ² 16AWG TO 14AWG
2359527-2	4.0mm ² 12AWG
2359527-3	18AWG

2. MATERIALS:
PLASTICS: PBT+PC ALLOY, UL-V0, UV-FI
CONTACTS: COPPER ALLOY, TIN PLATED
SCREWS : STAINLESS STEEL
3. OPERATING RATINGS :
VOLTAGE (max): 600Vac Max
CURRENT (max): 25A ON 4.0mm² & 20A ON 12AWG
TEMPERATURE : -40°C TO 85°C
IP RATING : IP67 & IP68
4. FOR ASSEMBLY INSTRUCTIONS, REFER APPLICATION SPECIFICATION 114-133123
5. PACKAGING: MOQ 200 pcs IN PE BAG





PRODUCT UNDER TESTING

CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

POLARIZING KEY A
2379239-1
1-2379239-1




KEYS

POLARIZING KEY B
2379239-2
1-2379239-2



BACKSHELL FOR
2379239-1
2379239-2

BACKSHELL FOR
1-2379239-1
1-2379239-2




2363547-2	2365125-2	KEY B	Ø 7 - Ø 10	IN-LINE SOCKET CONNECTOR	1-2379239-2
	2365125-1	KEY A			1-2379239-1
2363547-1	2365125-2	KEY B	Ø 10.5 - Ø 15		2379239-2
	2365125-1	KEY A			2379239-1
BACKSHELL P/N	HOUSING ASSY P/N	POLARIZING KEY	CABLE RANGE	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUBHASH. M 28AUG2020	TE Connectivity		
		CHK M. ZUCCA 28AUG2020			
		APVD PETER OTT 24NOV2020	NAME NECTOR T, 3Pos, SOCKET CONNECTOR CRIMP TYPE		
		PRODUCT SPEC -			
		APPLICATION SPEC -			
		WEIGHT -			
		CUSTOMER DRAWING	SIZE A3	CAGE CODE 00779	DRAWING NO C-2379239
		SCALE 2:1	SHEET 1 OF 2		REV AI


DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±0.2
	1 PLC ±0.2
	2 PLC ±0.1
	3 PLC ±
	4 PLC ±
	ANGLES ±1°
MATERIAL	FINISH
-	-
-	-


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

CRIMP TERMINATION
REFER 114-133123 FOR DETAILED INSTRUCTION
NOT TO SCALE



EXPLODED COMPONENTS
NOT TO SCALE



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUBHASH. M 28AUG2020	TE TE Connectivity			
DIMENSIONS: mm		CHK M. ZUCCA 28AUG2020				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD PETER OTT 24NOV2020	NAME NECTOR T, 3Pos, SOCKET CONNECTOR CRIMP TYPE		
	0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.1 3 PLC ± 4 PLC ± ANGLES ±1°		PRODUCT SPEC -			
	MATERIAL -		APPLICATION SPEC -			
	FINISH -		WEIGHT -			
-			SIZE A3	CAGE CODE 00779	DRAWING NO C-2379239	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 2:1	SHEET 2 OF 2	REV A1	