

RoHS

SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:500V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40°C to +105°C

Contact Material:Brass





Contact Plating:Au or Sn Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 5 seconds)

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

P	2	C	2	10	1	5	00	X	1256
产品类型 P=排针	间距 2=2.0	塑胶高度 C=2.0	排数 2=双排	单排PIN数 2~40P	产品形态 1=DIP	塑胶材料 2=LCP 5=PA6T	电镀厚度 00=带镀 01=AU1U	包装方式 1=管装 2=卷装 3=盘装 4=袋装 5=盒装	序列号

Dimension antitheses list							
ITEM	PA	PB	PW	PC	L	H	W
001	3.9			2.8	8.7	2.0	4.0
Alternate							

OPERATION

DRAW

SCALE

FIT

深圳市连盛精密连接器有限公司

X.X ±0.30

CHECK

UNIT

mm

X.XX ±0.20

APPROVE

SIZE

A4

X.XXX ±0.10

Angle

SHEET

1/1

±3°

DIM

PROJ.

◆

PART NO.

1010200342

TITLE:

2.0PH H=2.0 2x10P DIP PA3.9
PC2.8 L=8.7 AU0.6U PA6T

1

2

3

4

5

6

7

8

9