





Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE ± 0.05)



SPECIFICATIONS

Rated Current:7.0AMP

Contact Resistance:20m Ω Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000M Ω Min

Operation Temperature:-40°C to +105°C

Contact Material:Brass

Contact Plating:Au or Sn Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: LCP

Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

Ordering Information

PM 396 - * - N - Z - * - **

No.of Rows
1=Single Row
2=Dual Row

No.of Pins
2-20Pin

Type
Z=直针
和弯针
S=立贴
和S=插插

Length
(Pitch)

Contact Plating
G0:Gold Flash
G1:1u" Gold
G2:3u" Gold
G3:5u" Gold
G4:10u" Gold
G5:15u" Gold
G6:30u" Gold
S0:Gold Flash/Tin
S1:Tin

			GENERAL TOLERANCE		制 图	深圳市华灿天禄电子有限公司			
					DRAWING	ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核				
			X. X	± 0.30	批 准	产品名称	3.96单排 排母 直针(塑高8.89)	版 本	A
			X. XX	± 0.20	APPROVAL	TITLE		REV.	
			X. XXX	± 0.10	比 例	产品料号	PM396-1-N-Z-8.89-XX(L11.49)	单 位	mm
			Angle	$\pm 3.0^\circ$	SCALE	PART NO.		UNITS	
序号	变更内容	日期	投 影		Projection	材 料		页 次	1/1
No.	MODIFY CONTENT	MODIFY DATE				MATERIAL		SHEET	