




1.材料和电镀Materials and Finishes:
外 壳\Body - 黄铜\Brass,镀三元合金\Tri-matel plating
内导体\Contact - 铍铜\Beryllium copper,镀金\Gold plating
绝缘体\Insulator - 聚四氟乙烯\Teflon,本色\Natural
附 件\Accessories - 黄铜\Brass,镀三元合金\Tri-matel plating
密封圈\O-ring - 硅橡胶\Silicone rubber

2.电气性能Electrical:
A.特性阻抗\Impedance:50 Ohm
B.使用频率\Frequency range:DC-6GHz
C.介质耐压\Breakdown voltage:750V rms
D.绝缘电阻\Insulation resistance:5000 MΩ
3.机械性能\Mechanical:
A.使用寿命\Durability:500 cycles
B.中性盐雾\Salt spray:96 hours
C.防水等级\Waterproof level:内外IP67

推荐安装开孔



技术支持
13975145315



设 计	JAT	2024.01.03
审 核	DF	2024.01.03
批 准	DF	2024.01.03

料 号	CT6.1.55
规 格	TNC-MCX-KKYM-5
名 称	TNC母转MCX母穿墙安装
entitle® 深圳成泰电子有限公司 www.entitle.net	

*尺寸为重要尺寸

单位 mm