

1.材料和电镀Materials and Finishes:



- 外 壳\Body - 黄铜\Brass,镀金\Gold plating
内导体>Contact - 铍铜\Beryllium copper,镀金\Gold plating
绝缘体\Insulator - 聚四氟乙烯\Teflon,本色\Natural
压 圈\Tube - 黄铜\Brass,镀金\Gold plating


2.电气性能IElectrical:

- A.特性阻抗\Impedance:50 Ohm
B.使用频率\Frequency range:DC-4GHz
C.介质耐压\Breakdown voltage:750V rms
D.绝缘电阻\Insulation resistance:5000 MΩ

3.机械性能MEchanical:

- A.使用寿命\Durability:500 cycles



技术详询 139-7514-5315					版次	V1.1	比例	6:1	料号	CT4.1.68			
					第一角法						规格	MCX-KFD	
											名称		MCX四孔法兰母头
设计	JAT	2024.01.06	 深圳成泰电子有限公司 www.entitle.net										
审核	DF	2024.01.06											
批准	DF	2024.01.06											
			*尺寸为重要尺寸		单位		mm						