

1.材料和电镀Materials and Finishes:



- 外 壳Body - 黄铜\Brass,镀三元合金\Tri-matel plating
内导体\Contact - 铍铜\Beryllium copper,镀金\Gold plating
绝缘体\Insulator - 聚四氟乙烯Teflon,本色\Natural
其 他\Accessories - 铜材\Copper,镀三元合金\Tri-matel plating
密封圈\Gasket- 硅橡胶\Silicone rubber

2.电气性能Electrical:

- A.特性阻抗\Impedance:N/A
B.使用频率\Frequency range:DC-300 MHz
C.介质耐压\Breakdown voltage:5000V rms
D.绝缘电阻\Insulation resistance:5000 MΩ

3.机械性能Mechanical:

- A.使用寿命\Durability:500 cycles
B.中性盐雾\Salt spray:96 hours



技术支持 13975145315 		设计	JAT	2024.01.03	 	版次	 第一角法	比例	3:1		料号	CT4.1.60
		审核	DF	2024.01.03		规格		SHV-C-K5				
批准	DF	2024.01.03	*尺寸为重要尺寸			单位		mm	名称		SHV母接CTGY-5KV高压线	
 深圳成泰电子有限公司 www.entitle.net												