





RoHS

TABLE B:

PIN NO.	PIN NAME
C1	Supply Voltage Vcc
C2	Rest(RST)
C3	Clock(CLK)
C4	RFU
C5	Ground(GND)
C6	Programming Voltage Vpp
C7	I/O
C8	RFU



RECOMMENDED PCB LAYOUT
TOLERANCES:±0.05

Specifications/技术规格:

- 1.Current rating/额定电流: 1.0A
- 2.Voltage rating/额定电压: 10V AC/DC
- 3.Insulation Resistance/绝缘电阻: 1000MΩ Min
- 4.Dielectric Withstanding/ 耐电压: 500V AC/minute
- 5.Contact Resistance/ 接触电阻: 100mΩ Max
- 6.Durability/ 耐久性: 5,000 Insertions
- 7.Operating Temperature/ 工作温度: -40℃ to +85℃

④	Contact		6	Phosphor bronze	Au plated
③	Terminal		6	Phosphor bronze	Sn plated
②	Cover		1	SUS	Ni plated
①	Base		1	LCP	Black
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co.,Ltd

design	date	name	SIM CARD CONNECTOR
Review	date	model	SIM-302A
Approved	date		

Drawing number: A4

REFERENCE SIM CARD PLUG

INSERT USIM CARD