



N=PIN数



材料Material

原料Insulator:PBT/PA9T/6T (UL 94V-0)

相关材料Related Material: Brass

表面涂层Surface Coating: Au Over Ni

规格Specification

额定电流Current rating:2.5AMP

耐压Dielectric Withstanding Voltage:1000v Ac Min

绝缘电阻Insulation Resistance:1000MΩ min

接触电阻Contact resistance:20MΩ Max

工作温度Working Temperature:-45℃~+105℃

Max.Processing Temp瞬时温度:

PBT 230° ± 5° 10S

PA6T/9T 260° ± 5° 10S

P.C.B LAYOUT

L	PC	PA	L	PC	PA
11.2	3.0	5.7	19.0	3.0	13.5
11.6	3.0	6.1	20.0	3.0	14.5
12.0	3.0	6.5	21.0	3.0	15.5
13.0	3.0	7.5	22.0	3.0	16.5
14.0	3.0	8.5	23.0	3.0	17.5
15.0	3.0	9.5	24.0	3.0	18.5
16.0	3.0	10.5	25.0	3.0	19.5
17.0	3.0	11.5			
18.0	3.0	12.5			

		上海洲日电子有限公司	
		Shanghai Zhouri Electronics CO.,LTD	
		上海康司玛电子设备进出口有限公司	
		Shanghai KangSiMa Electronic Equipment import and export Co.,LTD	
绘图:	NIU	日期:2024-06-28	tel:021-51571121 http://www.zhour.net
审核:	ZHANG	日期:2024-06-28	fax:021-51571120 http://www.ksmchina.com
版本编号:	ZRLCGY2024-06-28-CJ/A1	产品名称:	PZ2.54-2xN-L
第三视角:		单位: mm	比例: 图幅:A4 页次 共 01 第 01