





SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:−40°c to +105°c

Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V−0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30−60 seconds
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list			
ITEM	PA	PC	L
Standard	6.00	3.00	11.50
Alternate			

				OPERATION		DRAW	小卢	2016.9.9	SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30				UNIT	mm		
				X.XX	±0.20	CHECK			SIZE	A4		
AO	2012.03.28	NEW DRAWING		X.XXX	±0.10				SHEET	1/1	PART NO.	1010300057
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	Angle	APPROVE			PROJ.		TITLE:	2.54PH H=2.5 2x18P DIP PA6.0 PC3.0 L=11.5 AU0.6U PA6T
					DIM				TOL			

B

D

E

F

G

A