



N=PIN数

材料Material

原料Insulator:PBT/PA9T/6T (UL 94V-0)

相关材料Related Material: Brass

表面涂层Surface Coating: Au Over Ni

规格Specification

额定电流Current rating:2.5AMP

耐压Dielectric Withstanding Voltage:1000v Ac Min

绝缘电阻Insulation Resistance:1000MΩ min


接触电阻Contact resistance:20MΩ Max

工作温度Working Temperature:-45°C~+105°C

Max.Processing Temp瞬时温度:

PBT 230° ± 5° 10S

PA6T/9T 260° ± 5° 10S



P.C.B LAYOUT

L	PC	PA	L	PC	PA
11.2	3.0	5.7	19.0	3.0	13.5
11.6	3.0	6.1	20.0	3.0	14.5
12.0	3.0	6.5	21.0	3.0	15.5
13.0	3.0	7.5	22.0	3.0	16.5
14.0	3.0	8.5	23.0	3.0	17.5
15.0	3.0	9.5	24.0	3.0	18.5
16.0	3.0	10.5	25.0	3.0	19.5
17.0	3.0	11.5			
18.0	3.0	12.5			

上海洲日电子有限公司 Shanghai Zhouri Electronics CO.,LTD 上海康司玛电子设备进出口有限公司 Shanghai KangSiMa Electronic Equipment import and export Co.,LTD		tel:021-51571121		http://www.zhour.net	
		fax:021-51571120		http://www.ksmchina.com	
		产品名称:		PZ2.54-1xN-L	
		版本编号: ZRLCGY2024-06-28-CJ/A2			
绘图:	NIU	日期:	2024-06-28		
审核:	ZHANG	日期:	2024-06-28		
第三视角:		单位:	mm		比例:
		图幅:	A4		页次 共 01 第 01