






RoHS



LOCK CARD TATUS



OPEN CARD TATUS




RECOMMENDED P.C.B HOLE LAYOUT
COMPONENT SIDE VIEW(TOLERANCE: ± 0.05)

产品外形 焊盘


PIN NO.	NAME	PIN NO.	NAME
C1	VCC	C4	VPP
C2	GND	C5	CLK
C3	RST	C6	IO

Specifications/技术规格:

- 1.Current rating/额定电流: 1.0A
- 2.Voltage rating/额定电压: 50V DC
- 3.Insulation Resistance/绝缘电阻: 100M Ω Min
- 4.Dielectric Withstanding/耐电压: 500V AC/minute
- 5.Contact Resistance/接触电阻: 60m Ω Max
- 6.Durability/耐久性: 5,000 Insertions
- 7.Operating Temperature/工作温度: -25°C to $+85^{\circ}\text{C}$



MICRO SIM



①	Contact point		6	Phosphor bronze	Au Plated
②	Terminal		6	Phosphor bronze	Au Plated
③	Cover		1	SUS	
④	Base		1	LCP	Black
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co.,Ltd

design	date	name	MICRO SIM CARD CONNECTOR
Review	date	model	MICRO-SIM-006-H18
Approved	date		

Drawing number: Proportion 1:1 unit mm gage number A4

modify Review Approved

angle	$\pm 2^{\circ}$
10~30	± 0.30
5~10	± 0.20
~ 5	± 0.10

Tolerance not specified

RoHS

24.00±0.40

ø100

ø330

LABEL

ADHESIVE TAPE
4 PLC

400 MIN.

PEELING ANGLE
160°~180°

ABOUT 300mm MIN LONG

15PCS UNLOADED SECTION

PRODUCT LOADING SECTION

15PCS UNLOADED SECTION

ABOUT 400mm MIN. LONG

TOP OF TAPE

20.00

24.00

PULL OUT DIRECTION

0.30

2.0

PARTITION

TAPE & REEL

10REEL

VOID FILLER

PARTITION

CARTON
DIMENSIONS
350×350×310

YUANDI® Yuandi Electronics Co.,Ltd

design	date	name	MICRO SIM CARD CONNECTOR
Review	date	model	MICRO-SIM-006-H18
Approved	date		

Drawing number:	Proportion	1:1	unit	mm	gape number	A4
-----------------	------------	-----	------	----	-------------	----

angle	±2°
10~30	±0.30
5~10	±0.20
~ 5	±0.10

modify	Review	Approved	Tolerance not specified
--------	--------	----------	-------------------------