



RoHS







(0.65±0.3) PUSH STROKE POSITION
(1.50±0.3) CARD LOCK POSITION
(4.20±0.3) CARD EJECT POSITION



NANO SIM CARD

SIM pin assignment	
PIN#	Name
C1	VCC供电电压
C2	RST重置
C3	CLK时钟
C5	GND接地
C6	VPP程序电压
C7	I/O输入输出
CD	Detect Switch



RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05

▨ PAD
▩ KEEP OUT AREA

Specifications/技术规格:

- 1.Current rating/额定电流: 1.0A
- 2.Voltage rating/额定电压: 30V AC/DC
- 3.Insulation Resistance/绝缘电阻: 100MΩ Min 500V DC
- 4.Dielectric Withstanding/ 耐电压: 500V AC/minute
- 5.Contact Resistance/ 接触电阻: 100mΩ Max
- 6.Durability/ 耐久性: 5,000 Insertions
- 7.Operating Temperature/ 工作温度: -40℃ to +85℃

Ⓕ	Terminal		7	Phosphor bronze	Au plated
Ⓖ	Bullet		1	SUS	
Ⓓ	Spring		1	SUS	
Ⓒ	Contact		7	Phosphor bronze	Au plated
Ⓑ	Cover		1	SUS	Ni Plating
Ⓐ	Base		1	LCP	Black
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co.,Ltd

design	date	name	NANO SIM CARD CONNECTOR
Review	date	model	NANO-SIM-500B
Approved	date		

Drawing number: Proportion 1:1 unit mm gage number A4


modify Review Approved

angle	±2°
10~30	±0.30
5~10	±0.20
~ 5	±0.10

Tolerance not specified


RoHS

客户拉出方向



客户拉出方向

自粘上贴



PE袋

纸箱底部和顶部各垫一块珍珠棉

护角


纸箱

封箱胶带“工”字形封好

将10卷产品放入箱内

NOTES

1. 每卷包装数量:1500PCS/每卷
2. 卷带包装方式:



3. 每箱包装数量:15000PCS/箱

4. 纸箱350mm*350mm*340mm(内部尺寸), 材质K=K

YUANDI® Yuandi Electronics Co.,Ltd

design	date	name	NANO SIM CARD CONNECTOR
Review	date	model	NANO-SIM-500B
Approved	date		

Drawing number: Proportion 1:1 unit mm gape number A4

modify Review Approved

angle	±2°
10~30	±0.30
5~10	±0.20
~ 5	±0.10

Tolerance not specified