

RoHS

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance:20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40°c to +105°c

Contact Material:Brass





Contact Plating:Au Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Dimension antitheses list			
ITEM	PA	PC	L
Standard	6.00	3.00	11.50
Alternate			

2x11P

深圳市连盛精密连接器有限公司

				OPERATION		DRAW		SCALE		FIT			
				X.X	±0.30			UNIT	mm				
				X.XX	±0.20	CHECK		SIZE	A4				
				X.XXX	±0.10			SHEET	1/1				
				Angle	±3°	APPROVE		PROJ.	◆				
				DIM	TOL								
A0	2012.03.28	NEW DRAWING										PART NO.	1010300194
REV	DATE	MODIFICATION DESCRIPTION		CHANGE								TITLE:	2.54PH H2.5mm 2xNP 180°