








REV.	ECN NO OR DESCRIPTION	DRAW	DATE



CIRCUIT DIAGRAM



PCB.WELDING DRAWING



主要技术参数、性能
The Main Thchnology Performance

额定电流、电压 Rate voltage,current	50mA DC12V
接触电阻 Contact resistance	≤100mΩ
按力 Operating force	±50gf
行程 travel	0.2±0.1mm
绝缘电阻 Insulated resistance	≥100MΩ
介电强度 Dielectric strength	≥250VAC/1min

Part No	H(高度)	克力	Part No	H(高度)	克力
SMG-06-H020A0	2.00	250gf	SMG-06-H025A0	2.50	250gf
SMG-06-H020B0	2.00	180gf	SMG-06-H025B0	2.50	180gf

F	按钮	LCP	1	黑色
E	盖板	不锈钢	1	清洗
D	防尘胶	聚酰亚胺	1	橙黄色
C	弹片	不锈钢	2	镀银
B	本体	LCP	1	黑色
A	卡件	磷铜	1	镀银
项目 ITEM	名称 DESCRIPTION	材质 MATERIAL	数量 QTY	表面处理/颜色 FINSH/COLOR

GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM	TITLE:	PART NO.	
		3.0*4.0*X贴片	SMG-06-HXXXX0	
DISTANCE	ANGLE	Matthew	 SM switch Co.,Ltd. 无锡斯茂科技有限公司 ISO 9001/ISO14001	
X. ±0.30	X.° ±2.0°	Benjamin		
.X ±0.20	.X° ±1.0°	Michael		
.XX ±0.15	.XX° ±0.5°	/		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	Alexander	 THIRD ANGLE PRDJECTION		SHEET NO 1 OF 1
	Sophia			