







REV.	ECN NO OR DESCRIPTION	DRAW	DATE



CIRCUIT DIAGRAM



PCB.WELDING DRAWING



主要技术参数、性能
The Main Thchnology Performance

额定电流、电压 Rate voltage,current	50mA DC12V
接触电阻 Contact resistance	≤100mΩ
按力 Operating force	±50gf
行程 travel	0.2±0.1mm
绝缘电阻 Insulated resistance	≥100MΩ
介电强度 Dielectric strength	≥250VAC/1min

Part No	H(高度)	Part No	H(高度)
SMG-02T-H035A0	3.50	SMG-02T-H050A0	5.00
SMG-02T-H038A0	3.80	SMG-02T-H055A0	5.50
SMG-02T-H043A0	4.30	SMG-02T-H060A0	6.00
SMG-02T-H045A0	4.50		

E	按钮	PPA	1	黑色
D	盖板	铁盖	1	镀铜锡
C	弹片	不锈钢	1	镀银
B	本体	PPA	1	黑色
A	卡件	黄铜	1	镀银
项目 ITEM	名称 DESCRIPTION	材质 MATERIAL	数量 QTY	表面处理/颜色 FINSH/COLOR

GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM	TITLE: 4.5*4.5*X贴片 250GF	PART NO. SMG-02T-HXXXXA0	
DISTANCE	ANGLE	 SM switch Co.,Ltd. ISO 9001/ISO14001 无锡斯茂科技有限公司		
X. ±0.30	X.° ±2.0°			
.X ±0.20	.X° ±1.0°			
.XX ±0.15	.XX° ±0.5°			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	Alexander	THIRD ANGLE PRDJECTION	SHEET NO 1 OF 1	
	Sophia			