



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 60249-1
FF 250 REC 16-12AWG BR

Also in the Series

Customers Also Bought



TE Part #2-2176050-0
RLP73N 1E R33 5% 5K RL



TE Part #1-1879216-5
CPF 0402 69K8 0.1% 25PPM 1K RL



TE Part #2106003-3
Connector, SMT-IDC, 3 position, 18AWG



TE Part #2176346-9
CRGCQ 1210 22R 5%



TE Part #2-1416010-4
RE034006

TE Part #4515-DS3A010GPF
PRESS XDCR,ANALOG,INH20 RANGE

TE Part #A1004BR22P1
NTC THERMISTOR ASSEMBLY

TE Part #A1004BR22P3
NTC THERMISTOR ASSEMBLY

TE Part #A1004BT22P2
NTC THERMISTOR ASSEMBLY

Documents

Product Drawings
VCF4-1000=FROM SEC

English

CAD Files
Customer View Model
ENG_CVM_CVM_1393310-3_B.2d_dxf.zip



English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1393310-3_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1393310-3_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Automotive Relay Application Notes](#)

English

[Connectors for Mini ISO, Connectors Production Production North America, Accessories](#)

English

Product Specifications

[Definitions General Purpose Relays](#)

English