

NOTES 注释:

1. MATERIAL 材料:
 - 1.1 INSULATION 绝缘材料: PA9T (KUARARY GN2330) WITH 30% GF, UL94V-0, COLOR 颜色: SEE PART No..
 - TINE PLATE 齿板: LCP (ZENITE 5145L OR E471i) WITH 30% GF, UL94V-0, COLOR 颜色: SEE PART No..
 - 1.2 CONTACTS 触点: PHOSPHOR BRONZE, C5191R-H, T=0.25mm
2. FINISH 饰面:
 - 2.1 CONTACT 触点: SELECTEIVE GOLD PLATING ON CONTACT AREA. 100µ" MIN. MATTE TIN PLATING ON SOLDER TAILS 50µ" MIN. NICKEL UNDERPLATING OVERALL.

X3091 W R - XX X - 9T V01

- ① ② ③ ④ ⑤ ⑥ ⑦


- ① Series Nunber
- ② Terminal form: WAFER
- ③ Welding Board Angle : R-90°
- ④ No. of Pins: XX-36~164 Pin
- ⑤ Tail Length (DIM "E") /A :2.30mm B:3.1mm
- ⑥ Plastic material: PA9T/PA46 UL94V-0
- ⑦ Contact Plating: V01-Gold Flash V15-Gold 15"u" V30-Gold 30"u"

DIMENSIONS				
POSITION	N	B±0.15	C±0.15	D±0.23
36	6	7.65	9.15	25.00
64	20	21.65	23.15	39.00
98	37	38.65	40.15	56.00
164	70	71.65	73.15	89.00



MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGLAR ±5°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5



DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	PART NO.: X3091WR-XXX-9TV01
CHKD		UNIT: mm/in	DWG NO.: X-X3091WR-XXX-9TV01
APPD		SIZE: A4	WEIGHT SHEET REVISION
XKB INDUSTRIAL PRECISION CO., LIMITED			1/1 A0



DIMENSIONS				
POSITION	N	C	F±0.20	G
36	6	9.15	8.15	B PIN#17
64	20	23.15	22.15	B PIN#31
98	37	40.15	39.15	B PIN#48
164	70	73.15	72.15	B PIN#81



RECOMMENDED PCB LAYOUT (TOP VIEW)

TOLERANCE: ±0.05

DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	PART NO.:
CHKD		UNIT: mm/in	X3091WR-XXX-9TV01
APPD		SIZE: A4	DWG NO.:
			X-3091WR-XXX-9TV01
		WEIGHT	SHEET
			REVISION



XKB INDUSTRIAL PRECISION CO., LIMITED