

广东星坤科技股份有限公司



Δ	日期
Δ	日期
Δ	日期
Δ	日期

文件工程章


MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
	REVISIONS				
					ANGLAR ±5°
					L ≤ 4 ±0.2
					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5



DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	PART NO.: X9414WWS-288T2-9TV15
CHKD	UNIT: mm/in	DWG NO.: X-X9414WWS-288T2-9TV15
APPD	SIZE: A4	WEIGHT SHEET REVISION
XKB INDUSTRIAL PRECISION CO., LIMITED		1/1 A0



RECOMMENDED PCB LAYOUT (TOP VIEW)
FOR 3 BOARDLOCKS



RECOMMENDED PCB LAYOUT (TOP VIEW)
FOR 3 TABS

-Z-

广东星坤科技股份有限公司


Δ#	日期
ΔX	日期
ΔX	日期

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
	REVISIONS				
					ANGLAR ±5°
					L ≤ 4 ±0.2
					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5



DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	PART NO.: X9414WVS-288T2-9TV15
CHKD	UNIT: mm/in	DWG NO.: X-X9414WVS-288T2-9TV15
APPD	SIZE: A4	WEIGHT SHEET REVISION
KKB INDUSTRIAL PRECISION CO., LIMITED		1/1 A0



20.70	147.50	158.50	162.00	LONG
20.30	145.50	156.00	156.00	MIDDLE
20.20	142.00	151.50	152.00	SHORT
DIM.D	DIM.C	DIM.B	DIM.A	LATCH TYPE

X9414 W V S - 288 T 2 - 9T V15

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ① Series Number
- ② Terminal form: WAFER
- ③ Welding Board Angle : V-Stright Angle 180°
- ④ Welding Way:S-SMT
- ⑤ No.of Pins: 288PIN
- ⑥ BOARDLOCK TYPE: B.BOARD LOCKS TYPE
T.TAB type
- ⑦ LATCH TYPE: 1.short latch;2.long latch;3.middle latch
- ⑧ Plastic material: PA9T
- ⑨ Contact Plating:V15 15"u";V30 30"u"

NOTES 注释:

1. MATERIAL材料:
 - 1.1 HOUSING外壳: HIGH PERFORMANCE RESINS, GLASS FILBER,UL94V-0;COLOR:BLACK.
 - 1.2 LATCH锁: HIGH PERFORMANCE RESINS, GLASS FILBER, UL94 V-O;COLOR: BLACK.
 - 1.3 CONTACTS触点: COPPER ALLOY.
 - 1.4 BOARDLOCK针脚: STAINLESS STEEL.
 - 1.5 TABS标签: STAINLESS STEEL.
2. FINISH饰面:
 - 2.1 CONTACT触点:
 - [SEE PART NO..] GOLD PLATING ON THE CONTACT AREA.
 - 2.54um [100u"] MIN. MATTE-TIN PLATING ON THE SOLDERING AREA
 - 1.27um [50u"] MIN. NICKEL UNDERPLATING OVERALL.

广东星坤科技股份有限公司

姓名	日期
数量	日期
MARK	DESCRIPTION
文件	工程章

					ANGLAR	±5°
					L ≤ 4	±0.2
					4 < L ≤ 16	±0.3
					16 < L ≤ 63	±0.4
					L > 63	±0.5
REVISIONS						UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	PART NO.: X9414WVS-288T2-9TV15
CHKD		UNIT: mm/in	DWG NO.: X-X9414WVS-288T2-9TV15
APPD		SIZE: A4	WEIGHT SHEET REVISION
XKB INDUSTRIAL PRECISION CO., LIMITED			1/1 A0