



Part Number : 1552209019


Series Number : 155220
Product Category : Industrial Cable

Product Description : Flamar Distribution Box Cable, WSOR Jacket, Unshielded, 19 Circuits, 3x(0.75mm²) with Green-Yellow Ground + 16x(0.34mm²) / 3x(19 AWG) with Green-Yellow Ground + 16x(22 AWG), 10.20mm (.402") Diameter, 100.0m (328.08') Length, Black
Status : New Business Not Supported
Engineering Number : B80-19-1X100M

Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	New Business Not Supported
--------	----------------------------

Category	Industrial Cable
Series	155220
Description	Flamar Distribution Box Cable, WSOR Jacket, Unshielded, 19 Circuits, 3x(0.75mm ²) with Green-Yellow Ground + 16x(0.34mm ²) / 3x(19 AWG) with Green-Yellow Ground + 16x(22 AWG), 10.20mm (.402") Diameter, 100.0m (328.08') Length, Black
Geographic Area	Global
Product Family	Flamar Standard and Custom Cables for Industrial Automation
Product Name	Flamar,Signal and Control
UPC	889056463478

Agency

UL	E172949
----	---------

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	600V

Physical

Bending Radius - Minimum	> 10xOD
Cable Length	100.0m
Circuits (Loaded)	19 (3+16)
Color - Cable Jacket	Black
Insulation	TPE
Material - Outer Jacket	WSOR
Net Weight	0.151/kg
Outer Jacket Diameter	10.20mm
Packaging Type	Reel
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	UL AWM 21215 / CSA
Wire Size (AWG)	19, 22
Wire Size mm ²	0.34, 0.75

This document was generated on Apr 15, 2024