



Part Number : 150180358

Series Number : 15018

Product Category : Flexible Printed Circuit (FPC) Flex Jumpers

Product Description : 0.50mm Pitch Premo-Flex FFC Jumper with Ears, Opposite Side Contacts (Type D), 305.00mm Cable Length, Gold (Au) Plating, 32 Circuits

Status : Active

Documents & Resources

Drawings

Drawing 150180358\_sd.pdf

Specifications

Product Specification 150180001-000.pdf

Product Environment Compliance

Compliance

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                          |
| China RoHS         |  |
| EU ELV             | Not Relevant                                                                          |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21                                                    |
| REACH SVHC         | Not Contained per D(2023)8585-DC (23 Jan 2024)                                        |
| EU RoHS            | Compliant per EU 2015/863                                                             |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Part Details

### General

|                |                                                                                                                                      |
|----------------|--------------------------------------------------------------------------------------------------------------------------------------|
| Status         | Active                                                                                                                               |
| Category       | Flexible Printed Circuit (FPC) Flex Jumpers                                                                                          |
| Series         | 15018                                                                                                                                |
| Description    | 0.50mm Pitch Premo-Flex FFC Jumper with Ears, Opposite Side Contacts (Type D), 305.00mm Cable Length, Gold (Au) Plating, 32 Circuits |
| Comments       | Contacts on opposite sides, Type D                                                                                                   |
| Product Family | FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers                                                                            |
| Product Name   | Premo-Flex FFC Jumper                                                                                                                |
| UPC            | 193264331826                                                                                                                         |

### Electrical

|                               |        |
|-------------------------------|--------|
| Current - Maximum per Contact | 0.5A   |
| Voltage - Maximum             | 60V AC |

### Physical

|                               |                    |
|-------------------------------|--------------------|
| Cable Length                  | 305.00mm           |
| Circuits (Loaded)             | 32                 |
| Contact Layout Type           | D (opposite side)  |
| Design Feature                | Superior Retention |
| Material - Plating Mating     | Gold               |
| Packaging Type                | Bag                |
| Pitch - Mating Interface      | 0.50mm             |
| Temperature Range - Operating | -40° to +105°C     |
| Wire/Cable Type               | Flat Flex Cable    |
| Wire Size (AWG)               | N/A                |

---

### Mates With / Use With

Mates with Part(s)

| Description                                                                                                                               | Part Number       |
|-------------------------------------------------------------------------------------------------------------------------------------------|-------------------|
| Easy-On FFC/FPC Connector<br>0.50mm Pitch, FD19 Series, Right-Angle, Bottom Contact, 1.90mm Height, 32 Circuits, Gold over Nickel Plating | <u>5051103291</u> |