



NOTES:

- MATERIAL**
 - 1-1: SUS-301 THICKNESS=0.10MM
- SPECIFICATIONS**
 - 2-1: RATED CURRENT: 1.0A
 - 2-2: VOLTAGE RATING: 1.5V
 - 2-3: CONTACT RESISTANCE: 80mΩ/MAX
 - 2-4: WELDING THRUST: >3KG
 - 2-5: OPERATING TEMPERATURE: -40°C~+85°C
- DURABILITY:** 1500 CYCLES
- SALT SPRAY TIME:** 24H
- ELECTROPLATE:** THE NICKEL-PLATED SUBSTRATE IS 50μ MIN
- REQUIREMENTS**
 - 6-1: TERMINAL TO EAT FULL TIN, NOT PEELING, WELDING OBVIOUS COLOR AND OTHER ADVERSE
 - 6-2: ROHS, REACH, HF HALOGEN ADVERSE OF DOMESTIC AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS




RECOMMENDED PCB LAYOUT
TOLERANCE: ±0.05MM (FOR REFERENCE ONLY)

METAL MASK T=0.08
TOLERANCE: ±0.05MM (FOR REFERENCE ONLY)


MANUFACTURE DWG	
UNLESS OTHERWISE SPECIFIED TOLERANCES	
DECIMALS: X.:±0.30 X.X:±0.20 X.XX:±0.15	ANGLES: X.°:±2° X.X°:±1° X.XX°:±0.5°
TITLE: 天线弹片 L.1.90*W1.00*H2.30 PAR ASP-D2301-BE1 DWN Lucas CHKD Ethan APVD Jacob SCALE1:1 UNIT:MM CUSTOMER COPY SIZE:A4 SHEET:1F1 REV:A	



3D View



(For Reference Only)
Stated At Compression



OTES:

MATERIAL

-1: SUS-301 THICKNE=0.10MM

SPECIFICATIONS

-1: RATED CURRENT: 1.0A

-2: VOLTAGE RATING: 1.5V

-3: CONTACT RESISTANCE: 80mΩ/MAX

-4: WELDING THRUST: ≥3KG

2-5: OPERATING TEMPERATURE

DURABILITY: 1500 CYCLES

SALT SPRAY TIME: 24H


ELECTROPLATE: THE REQUIREMENTS

1 TERMINAL TO EAT FULL TIN NOT FEELING


-1: TERMINAL TO EAT FULL TIN, NOT PEELING,
WELDING OBVIOUS COLOR AND OTHER ADVERSE

WELDING OBVIOUS COLOR AND OTHER ADVERSE
-2:ROHS.REACH.HF HALOGEN ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS

AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS



**RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)**



METAL MASK T=0.08
TOLERANCE: $\pm 0.05\text{MM}$
(FOR REFERENCE ONLY)

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES		 	TITLE: 天线弹片 L1.90*W1.00*H2.30	
DECIMALS:	ANGLES:		PAR	ASP-D2301-BE1
X.:±0.30	X.:±2°	DWN	Lucas	
X.X:±0.20	X.X*:±1°	CHKD	Ethan	
X.XX:±0.15	X.XX*:±0.5°	APVD	Jacob	
		SCALE1:1	UNIT:MM	
		CUSTOMER COPY	SIZE:A4	SHEET:1F1
				REV:A

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	
ROHS Compliant											MAPX	MODIFICATION	DATE	DRAW	APPROVE

