



Part Number : 732306220

Series Number : 73230

Product Category : RF Cable Assemblies

Product Description : MCX Right-Angle Plug-to-I-PEX MHF I LK Plug, 1.32mm Cable Diameter, 304.20mm Cable Length, 50 Ohms

Status : Active

Documents & Resources

Drawings  
Drawing 732306220\_sd.pdf

Product Environment Compliance

Compliance

|                    |              |
|--------------------|--------------|
| China RoHS         | Not Reviewed |
| EU ELV             | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC         | Not Reviewed |
| EU RoHS            | Not Reviewed |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

|          |                     |
|----------|---------------------|
| Status   | Active              |
| Category | RF Cable Assemblies |

|                        |  |
|------------------------|--|
| Series                 | 73230  |
| Description            | MCX Right-Angle Plug-to-I-PEX MHF I LK Plug, 1.32mm Cable Diameter, 304.20mm Cable Length, 50 Ohms |
| Assembly Configuration | Dual Ended Connectors  |
| Connector to Connector | MCX-to-I-PEX MHF   |
| Product Family         | RF Standard Cable Assemblies Solutions   |
| Product Name           | I-PEX MHF,MCX  |
| Type                   | RF Cable Assembly  |
| UPC                    | 196823189005   |

Electrical

|           |     |
|-----------|-----|
| Impedance | 50Ω |
|-----------|-----|

Physical

|                           |                 |
|---------------------------|-----------------|
| Cable Length              | 304.20mm        |
| Gender                    | Plug/Plug       |
| Material - Metal          | Brass           |
| Material - Plating Mating | Gold            |
| Net Weight                | 2.500/g         |
| Packaging Type            | Bag             |
| Single Ended              | No              |
| Wire/Cable Type           | 1.32mm, Coaxial |